

RF Power Pot Capacitors with Mounting Tags, Class 1 Ceramic



FEATURES

- Small size
- High reliability
- Wide range of capacitance values

APPLICATIONS

- Induction and dielectric heating
- Antenna units
- Filter, bypass, and coupling circuits

QUICK REFERENCE DATA

DESCRIPTION	VALUE						
Ceramic Class	1						
Ceramic Dielectric	R7, R16, R42, R85						
Type	TA 020030, TB 020030, TD 020030, TE 020030			TA 020050, TB 020050, TD 020050, TE 020050		TA 020080, TB 020080, TD 020080, TE 020080	
Voltage (V _p)	6000	7000	8000	7000	8000	7000	8000
Min. Capacitance (pF)	100	80	10	200	20	1200	40
Max. Capacitance (pF)	400	250	160	600	500	1200	1000
Mounting	Screw terminal						

MATERIAL

Capacitor elements made from class 1 ceramic dielectric with noble metal electrodes.

Connection terminals:
made from copper / brass, silver plated.

FINISH

Capacitor body completely protective lacquered.
The contoured insulating rim is additionally glazed.

MARKING

Type designator, capacitance value and tolerance, rated peak voltage, ceramic material code, production date code, manufacturer logo.

CAPACITANCE RANGE

10 pF to 1.2 nF

CAPACITANCE TOLERANCE

± 20 %; ± 10 %; ± 5 %

DIELECTRIC STRENGTH TEST

200 % of rated AC voltage (50 Hz, 5 minutes)

CERAMIC DIELECTRICS

- R7 (TCC + 100 ppm/K)
- R16 (TCC + 100 ppm/K)
- R42 (TCC - 250 ppm/K)
- R85 (TCC - 750 ppm/K)

RATED VOLTAGE

- 6.0 kV_p
- 7.0 kV_p
- 8.0 kV_p

DISSIPATION FACTOR

R7: max. 0.07 %
R16: max. 0.04 %
R42, R85: max. 0.05 %

Measuring frequencies:
1 MHz (< 1 nF); 300 kHz or 100 kHz (≥ 1 nF)

INSULATION RESISTANCE

Min. 100 000 MΩ (at 25 °C)

OPERATING TEMPERATURE RANGE

-55 °C to +100 °C







SAP PART NUMBER AND ELECTRICAL DATA						
PART NUMBER	CERAMIC	CAP. VALUES (pF)	RATED VOLTAGE (kV _p)	RATED POWER ⁽¹⁾ (kvar)	RATED CURRENT (A _{RM} S)	
TYPE T. 020030						
T#020030BP100##BF1	R7	10	8.0	3.5	6.0	
T#020030BP160##BF1		16				
T#020030BP200##BF1		20				
T#020030BP250##BG1	R16	25		4.2		
T#020030BP400##BG1		40				
T#020030BP500##BH1	R42	50				
T#020030BP600##BH1		60				
T#020030VY800##BH1		80	7.0			
T#020030BF101##BH1		100	6.0			
T#020030BP121##BJ1	R85	120	8.0			
T#020030BP161##BJ1		160				
T#020030VY201##BJ1		200	7.0			
T#020030VY251##BJ1		250	6.0			
T#020030BF301##BJ1		300				
T#020030BF401##BJ1		400				
TYPE T. 020050						
T#020050BP200##BF1	R7	20	8.0	5.6	6.0	
T#020050BP250##BF1		25				
T#020050BP400##BG1	R16	40				
T#020050BP500##BG1		50				
T#020050BP600##BG1		60				
T#020050BP800##BG1		80				
T#020050BP101##BH1	R42	100		7.0		
T#020050BP161##BH1		160				
T#020050VY201##BH1		200	7.0			
T#020050BP251##BJ1	R85	250	8.0			
T#020050BP301##BJ1		300				
T#020050BP401##BJ1		400				
T#020050BP501##BJ1		500				
T#020050VY601##BJ1		600				7.0
TYPE T. 020080						
T#020080BP400##BF1	R7	40	8.0	8.5		7.0
T#020080BP600##BF1		60				
T#020080BP800##BG1	R16	80				
T#020080BP101##BG1		100				
T#020080BP121##BG1		120				
T#020080BP161##BG1		160				
T#020080BP201##BH1	R42	200		10.5		
T#020080BP251##BH1		250				
T#020080BP301##BH1		300				
T#020080BP401##BJ1	R85	400				
T#020080BP501##BJ1		500				
T#020080BP601##BJ1		600				
T#020080BP102##BJ1		1000				
T#020080VY122##BJ1		1200	7.0			









Notes

- # 2nd digit: code letter of the terminal version A, B, D, E
 - ## 14th to 15th digit: capacitance tolerance code $\pm 20\%$ = 38, $\pm 10\%$ = 36, $\pm 5\%$ = 33
- (1) The surface temperature during operation must not exceed +100 °C









DIMENSIONS in millimeters (inches)









TA

TB

TD

TE


TYPE	T. 020030	T. 020050	T. 020080
Length L_1	30 (1.18)	50 (1.97)	80 (3.15)
Length L_2	15.0 ± 1.5 (0.591 ± 0.059)	25.0 ± 2.0 (0.984 ± 0.079)	40.0 ± 2.0 (1.575 ± 0.079)
Length L_3	20.0 ± 1.5 (0.787 ± 0.059)	25.0 ± 2.0 (0.984 ± 0.079)	40.0 ± 2.0 (1.575 ± 0.079)
Length L_5	31.0 ± 2.0 (1.220 ± 0.079)	51.0 ± 2.0 (2.008 ± 0.079)	81.0 ± 2.0 (3.189 ± 0.079)
Length L_6	36 (1.42)	56 (2.20)	86 (3.39)









DERATING DIAGRAMS
T#020030BP100##BF1

T#020030BP160##BF1

T#020030BP200##BF1

T#020030BP250##BG1

T#020030BP400##BG1

T#020030BP500##BH1

T#020030BP600##BH1

T#020030VY800##BH1










DERATING DIAGRAMS

T#020030BF101##BH1

T#020030BP121##BJ1

T#020030BP161##BJ1

T#020030VY201##BJ1

T#020030VY251##BJ1

T#020030BF301##BJ1

T#020030BF401##BJ1

T#020050BP200##BF1


DERATING DIAGRAMS
T#020050BP250##BF1

T#020050BP400##BG1

T#020050BP500##BG1

T#020050BP600##BG1

T#020050BP800##BG1

T#020050BP101##BH1

T#020050BP161##BH1

T#020050VY201##BH1


DERATING DIAGRAMS


T#020050BP251##BJ1

T#020050BP301##BJ1

T#020050BP401##BJ1

T#020050BP501##BJ1

T#020050VY601##BJ1

T#020080BP400##BF1

T#020080BP600##BF1

T#020080BP800##BG1


DERATING DIAGRAMS
T#020080BP101##BG1

T#020080BP121##BG1

T#020080BP161##BG1

T#020080BP201##BH1

T#020080BP251##BH1

T#020080BP301##BH1

T#020080BP401##BJ1

T#020080BP501##BJ1





DERATING DIAGRAMS


T#020080BP601##BJ1



T#020080BP102##BJ1



T#020080VY122##BJ1



RELATED DOCUMENTS

General Information

www.vishay.com/doc?22071



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.