

Optocoupler



Verification Certificate

This is to certify that:

Vishay Semiconductor GmbH
Theresienstrasse 2
Heilbronn
74072
Germany

Holds Certificate Number:

VC 641592

In respect of:

**BS EN 62368-1:2014 Audio/Video, information and communication Technology Equipment
Clauses 5.4, 5.5 & 6.4.5**

Type samples representative of the products listed have been tested and examined to the relevant requirements of the normative reference listed and have been found to comply with these requirements as detailed in the related Test Report as listed on page 2



For and on behalf of BSI:

Frank Lee, Product Certification Technical and Compliance Director

First Issued: 2016-01-11

Effective Date: 2021-11-23

Latest Issue: 2021-11-23

Expiry Date: 2023-07-02

Page: 1 of 4

...making excellence a habit.™

This certificate has been issued by and remains the property of BSI Assurance UK Ltd, Kitemark Court, Davy Avenue, Knowlhill, Milton Keynes MK5 8PP, United Kingdom and should be returned immediately upon request.
To check its validity telephone +44 (0) 345 080 9000. An electronic certificate can be authenticated [online](#).

BSI Assurance UK Limited, registered in England under number 7805321 at 389 Chiswick High Road, London W4 4AL, UK.
A member of BSI Group of Companies.



Verification Certificate

No. VC 641592

Manufacturing Location: Vishay Semiconductor Malaysia Sdn. Bhd.
No. 1710-1 Kawasan Perindustrian Krubong
75250 Melaka
Malaysia

Type Test Report Number: 3492972 Rev1

Product Description

Optocoupler types:

6N137, SFH6741, SFH6742, VO2601, VO2611, SFH6750, SFH6751, SFH6752, VO2630, VO2631 and VO4661

Optocouplers DIP8, 1-channel and 2-channels as listed below:

DIP8, 1-channel:	
(First part number)	(Second part number)
6N137	
SFH6741	VO2601
SFH6742	VO2611

DIP8, 2-channel:	
(First part number)	(Second part number)
SFH6750	VO2630
SFH6751	VO2631
SFH6752	VO4661

First Issued: 2016-01-11

Latest Issue: 2021-11-23

Effective Date: 2021-11-23

Expiry Date: 2023-07-02

Page: 2 of 4

This certificate has been issued by and remains the property of BSI Assurance UK Ltd, Kitemark Court, Davy Avenue, Knowlhill, Milton Keynes MK5 8PP, United Kingdom and should be returned immediately upon request.
To check its validity telephone +44 (0) 345 080 9000. An electronic certificate can be authenticated [online](#).

BSI Assurance UK Limited, registered in England under number 7805321 at 389 Chiswick High Road, London W4 4AL, UK.
A member of BSI Group of Companies.

Verification Certificate

No. VC 641592

Rated as below:

Standard models

	Basic and Supplementary Insulation	Reinforced Insulation
1. Hygroscopic/asbestos/natural rubber materials used:	No	No
2. Insulation system:	Basic / Supplementary	Reinforced
3. Mains supply voltage:	600 V r.m.s.	300 V r.m.s.
4. RMS working voltage	600 V r.m.s.	300 V r.m.s.
5. Peak working voltage:	2500 V	2500 V
6. Overvoltage category:	II	II
7. Pollution degree:	External 2 Internal 1	External 2 Internal 1
8. Maximum operating temperature:	110 °C	110 °C
9. Clearance distance:	≥3.6 mm	≥3.6 mm
10. Creepage distance:	≥6.0 mm	≥6.0 mm
11. Distance through insulation:	≥0.4 mm	≥0.4 mm
12. Comparative Tracking Index (CTI):	175 ≤ CTI ≤ 400	175 ≤ CTI ≤ 400
13. Material group:	IIIa	IIIa
Working parameters		
Mains transient voltage (Withstand voltage)	4000 V peak	2500 V peak
Thermal cycling storage temperature:	120 °C	120 °C
Thermal cycling electric strength test voltage.	4000 V peak	5000 V peak

First Issued: 2016-01-11

Latest Issue: 2021-11-23

Effective Date: 2021-11-23

Expiry Date: 2023-07-02

Page: 3 of 4

This certificate has been issued by and remains the property of BSI Assurance UK Ltd, Kitemark Court, Davy Avenue, Knowlhill, Milton Keynes MK5 8PP, United Kingdom and should be returned immediately upon request.

To check its validity telephone +44 (0) 345 080 9000. An electronic certificate can be authenticated [online](#).

BSI Assurance UK Limited, registered in England under number 7805321 at 389 Chiswick High Road, London W4 4AL, UK.
A member of BSI Group of Companies.

Verification Certificate

No. VC 641592

"Option 6" and "Option 7" models

	Basic and Supplementary Insulation	Reinforced Insulation
1. Hygroscopic/asbestos/natural rubber materials used:	No	No
2. Insulation system:	Basic / Supplementary	Reinforced
3. Mains supply voltage:	600 V r.m.s.	300 V r.m.s.
4. RMS working voltage	600 V r.m.s.	300 V r.m.s.
5. Peak working voltage:	2500 V peak	2500 V peak
6. Overvoltage category:	II	II
7. Pollution degree:	External 2 Internal 1	External 2 Internal 1
8. Maximum operating temperature:	110 °C	110 °C
9. Clearance distance:	≥3.6 mm	≥3.6 mm
10. Creepage distance:	≥6.0 mm	≥6.0 mm
11. Distance through insulation:	≥0.4 mm	≥0.4 mm
12. Comparative Tracking Index (CTI):	175 ≤ CTI ≤ 400	175 ≤ CTI ≤ 400
13. Material group:	IIIa	IIIa
Working parameters		
Mains transient voltage (Withstand voltage)	4000 V peak	2500 V peak
Thermal cycling storage temperature:	120 °C	120 °C
Thermal cycling electric strength test voltage.	4000 V peak	5000 V peak

In respect of BS EN 62368-1:2014 Clause 6.4.5, samples passed the flammability requirements in accordance with EN 60747-5-5:2001 Clause 7.4.3.6.1

Note: This certificate has been issued for the renewal of VC 641592.

First Issued: 2016-01-11

Effective Date: 2021-11-23

Latest Issue: 2021-11-23

Expiry Date: 2023-07-02

Page: 4 of 4

This certificate has been issued by and remains the property of BSI Assurance UK Ltd, Kitemark Court, Davy Avenue, Knowlhill, Milton Keynes MK5 8PP, United Kingdom and should be returned immediately upon request.
To check its validity telephone +44 (0) 345 080 9000. An electronic certificate can be authenticated [online](#).

BSI Assurance UK Limited, registered in England under number 7805321 at 389 Chiswick High Road, London W4 4AL, UK.
A member of BSI Group of Companies.