

Fast Recovery Diodes (Hockey PUK Version), 920 A, 1050 A



B-PUK (DO-200AB)

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	920 A, 1050 A
Package	B-PUK (DO-200AB)
Circuit configuration	Single

FEATURES

- High power fast recovery diode series
- 2.0 μ s to 3.0 μ s recovery time
- High voltage ratings up to 3000 V
- High current capability
- Optimized turn-on and turn-off characteristics
- Low forward recovery
- Fast and soft reverse recovery
- Press PUK encapsulation
- Case style conform to JEDEC® B-PUK (DO-200AB)
- Maximum junction temperature 150 °C
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

TYPICAL APPLICATIONS

- Snubber diode for GTO
- High voltage freewheeling diode
- Fast recovery rectifier applications

MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	SD1053C..L		UNITS
		S20	S30	
I _{F(AV)}		1050	920	A
	T _{hs}	55	55	°C
I _{F(RMS)}		1940	1700	A
I _{FSM}	50 Hz	15 000	13 000	
	60 Hz	15 700	13 610	
V _{RRM}	Range	1800 to 2500	1800 to 3000	V
t _{rr}		2.0	3.0	µs
	T _J	25		°C
T _J		-40 to +150		

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT $T_J = T_J$ MAXIMUM mA
VS-SD1053C..S20L	18	1800	1900	50
	22	2200	2300	
	24	2400	2500	
	25	2500	2600	
VS-SD1053C..S30L	18	1800	1900	
	22	2200	2300	
	25	2500	2600	
	28	2800	2900	
	30	3000	3100	

**FORWARD CONDUCTION**

PARAMETER	SYMBOL	TEST CONDITIONS	SD1053C..L		UNITS
			S20	S30	
Maximum average forward current at heatsink temperature	$I_{F(AV)}$	180° conduction, half sine wave Double side (single side) cooled	1050 (450)	920 (390)	A
Maximum RMS forward current	$I_{F(RMS)}$	25 °C heatsink temperature double side cooled	55 (85)	55 (85)	°C
Maximum peak, one-cycle forward, non-repetitive surge current	I_{FSM}	t = 10 ms	1940	1700	A
		No voltage reapplied	15 000	13 000	
		t = 8.3 ms	15 700	13 610	
		100 % V_{RRM} reapplied	12 620	10 930	
Maximum I^2t for fusing	I^2t	t = 10 ms	13 210	11 450	kA ² s
		No voltage reapplied	1125	845	
		t = 8.3 ms	1027	772	
		100 % V_{RRM} reapplied	796	598	
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	t = 0.1 to 10 ms, no voltage reapplied	727	546	kA ² √s
Low level value of threshold voltage	$V_{F(TO)1}$	(16.7 % $\times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)}$, $T_J = T_J$ maximum)	11 250	8450	V
High level value of threshold voltage	$V_{F(TO)2}$	($I > \pi \times I_{F(AV)}$, $T_J = T_J$ maximum)	1.34	1.51	
Low level value of forward slope resistance	r_{f1}	(16.7 % $\times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)}$, $T_J = T_J$ maximum)	1.48	1.67	mΩ
High level value of forward slope resistance	r_{f2}	($I > \pi \times I_{F(AV)}$, $T_J = T_J$ maximum)	0.37	0.50	
Maximum forward voltage drop	V_{FM}	$I_{pk} = 1500$ A, $T_J = T_J$ maximum, $t_p = 10$ ms sinusoidal wave	0.33	0.45	V

RECOVERY CHARACTERISTICS

CODE	MAXIMUM VALUE AT $T_J = 25$ °C	TEST CONDITIONS			TYPICAL VALUES AT $T_J = 150$ °C			
	t_{rr} AT 25 % I_{RRM} (μs)	I_{pk} SQUARE PULSE (A)	di/dt (A/μs)	V_r (V)	t_{rr} AT 25 % I_{RRM} (μs)	Q_{rr} (μC)	I_{rr} (A)	
S20	2.0	1000	100	- 50	4.0	400	180	
S30	3.0				4.5	550	230	

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating and storage temperature range	T_J, T_{Stg}		-40 to 150	°C
Maximum thermal resistance, case junction to heatsink	R_{thJ-hs}	DC operation single side cooled	0.073	K/W
		DC operation double side cooled	0.031	
Mounting force, ± 10 %			14 700 (1500)	N (kg)
Approximate weight			255	g
Case style		See dimensions - link at the end of datasheet	B-PUK (DO-200AB)	

 ΔR_{thJ-hs} CONDUCTION

CONDUCTION ANGLE	SINUSOIDAL CONDUCTION		RECTANGULAR CONDUCTION		TEST CONDITIONS	UNITS
	SINGLE SIDE	DOUBLE SIDE	SINGLE SIDE	DOUBLE SIDE		
180°	0.009	0.008	0.006	0.006	$T_J = T_J$ maximum	K/W
120°	0.011	0.011	0.011	0.011		
90°	0.014	0.014	0.015	0.015		
60°	0.020	0.021	0.021	0.022		
30°	0.036	0.036	0.036	0.036		

Note

- The table above shows the increment of thermal resistance R_{thJ-hs} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 4 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 5 - Current Ratings Characteristics




Fig. 3 - Current Ratings Characteristics




Fig. 6 - Current Ratings Characteristics




Fig. 7 - Current Ratings Characteristics




Fig. 10 - Forward Power Loss Characteristics




Fig. 8 - Current Ratings Characteristics




Fig. 11 - Forward Power Loss Characteristics




Fig. 9 - Forward Power Loss Characteristics




Fig. 12 - Forward Power Loss Characteristics




Fig. 13 - Maximum Non-Repetitive Surge Current




Fig. 16 - Maximum Non-Repetitive Surge Current Single and Double Side Cooled




Fig. 14 - Maximum Non-Repetitive Surge Current




Fig. 17 - Forward Voltage Drop Characteristics




Fig. 15 - Maximum Non-Repetitive Surge Current Single and Double Side Cooled




Fig. 18 - Forward Voltage Drop Characteristics




Fig. 19 - Thermal Impedance Z_{thJ-hs} Characteristic


Fig. 20 - Typical Forward Recovery Characteristics




Fig. 22 - Recovery Time Characteristics




Fig. 21 - Typical Forward Recovery Characteristics




Fig. 23 - Recovery Charge Characteristics




Fig. 24 - Recovery Current Characteristics




Fig. 27 - Recovery Current Characteristics




Fig. 25 - Recovery Time Characteristics




Fig. 28 - Maximum Total Energy Loss Per Pulse Characteristics




Fig. 26 - Recovery Charge Characteristics




Fig. 29 - Frequency Characteristics




Fig. 30 - Maximum Total Energy Loss
Per Pulse Characteristics




Fig. 33 - Frequency Characteristics




Fig. 31 - Frequency Characteristics




Fig. 34 - Maximum Total Energy Loss
Per Pulse Characteristics




Fig. 32 - Maximum Total Energy Loss
Per Pulse Characteristics




Fig. 35 - Frequency Characteristics




Fig. 36 - Maximum Total Energy Loss Per Pulse Characteristics




Fig. 38 - Maximum Total Energy Loss Per Pulse Characteristics




Fig. 37 - Frequency Characteristics




Fig. 39 - Frequency Characteristics

ORDERING INFORMATION TABLE

Device code	VS-	SD	105	3	C	30	S30	L
	1	2	3	4	5	6	7	8
1	Vishay Semiconductors product							
2	Diode							
3	Essential part number							
4	3 = fast recovery							
5	C = ceramic PUK							
6	Voltage code x 100 = V_{RRM} (see Voltage Ratings table)							
7	t_{rr} code							
8	L = PUK case B-PUK (DO-200AB)							

LINKS TO RELATED DOCUMENTS


Dimensions

www.vishay.com/doc?95246



B-PUK (DO-200AB)

DIMENSIONS in millimeters (inches)



Quote between upper and lower pole pieces has to be considered after application of mounting force (see Thermal and Mechanical Specifications)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.